



Highly Durable Rumen Trocar For Cow And Sheep Bloat With Different Needles

Basic Information

Place of Origin: China
 Brand Name: Chuangpu
 Model Number: HL-Q8B
 Minimum Order One Set

Quantity:

• Price: Negotiable

Packaging Details: Carton

• Delivery Time: 3-5 working days

• Payment Terms: T/T

• Supply Ability: 5000SETS/Month



Product Specification

Application: It Is Used To Exhaust The Rumen Of Cattle.

When The Rumen Bulges In Ruminants Such As Cattle, Sheep, Camels, Etc., The General Emergency Method Used Is The Rumen Puncture Method (exhaust Method)

Color: BlueLength: 12CM

• Feature: Three Kinds Of Needle For Different Animal

• Farm Animals Type: Cattle, Cow, Goat And Sheep

Needle Dia.: 2mm,3mm,3.5mmMaterial: Stainless Steel

• Highlight: Sheep Bloat Rumen Trocar,

Highly Durable Rumen Trocar,

Cow Rumen Trocar



More Images







Product Description

Corporate HQ: CHUANGPU ANIMAL HUSBANDRY TECHNOLOGY(SUZHOU) CO.,LTD

Export Dept: ZHANGJIAGANG FANRS MACHINERY CO.,LTD.

Branch: Sichuan Gene Haven Animal Husbandry Technology Co,Ltd

EMAIL: nancyzxd68@gmail.com sales2@dairymachinery.cc

MOBILE: +86 133 0156 9240(Wechat/WhatsApp)

OFFICE: +86 512 5890 5953

Product Description:

Our instrument features three different needles that are suitable for various animals. The Deflation Needle for Cattle Sheep is perfect for relieving bloating in these animals, while the bloat needle for cattle is specifically designed to help exhaust the rumen of cattle. When it comes to emergency veterinary procedures, having the right tools is crucial. Our Veterinary Instrument is not only durable and long-lasting but also easy to use. The blue color makes it easy to spot in a hurry, and the stainless steel material ensures a hygienic and safe product.

Features:

Product Name: Veterinary Instrument - - - - -

Length: 12CM

Material: Stainless Steel

Feature: Three Kinds Of Needle For Different Animal

Color: Blue

Application: It Is Used To Exhaust The Rumen Of Cattle. When The Rumen Bulges In Ruminants Such As Cattle, Sheep, Camels, Etc.,

The General Emergency Method Used Is The Rumen Puncture Method (exhaust Method)

Keywords: rumen puncture site, Gastric Exhaust Needle for Cattle, Puncture Needle for Veterinary Use

Technical Parameters:

Applicatio n	It is used to exhaust the rumen of cattle. When the rumen bulges in ruminants such as cattle, sheep, camels, etc., the general emergency method used is the rumen puncture method (exhaust method).
Needle Dia.	2mm, 3mm, 3.5mm
Feature	Three kinds of needle for different animal
Material	Stainless steel
Length	12CM
Farm Animals Type	Cattle, cow, goat, and sheep
Color	Blue

Applications:

The instrument features three kinds of needles with different diameters (2mm, 3mm, and 3.5mm) that are suitable for different animal sizes and types. The needles are made of stainless steel and are easy to sterilize to maintain a hygienic environment during the procedure. The instrument is 12cm long and has a blue color, which makes it easy to identify among other veterinary tools. The Chuangpu HL-Q8B Veterinary Instrument is an essential tool for veterinarians and animal professionals who perform rumen puncture procedures. Its reliable performance and high-quality construction make it a valuable asset in emergency situations, such as when sheep experience bloat puncture rumen, which can be life-threatening if not treated promptly. The HL-Q8B model is also ideal for performing gastric exhaust procedures in cattle, which is a standard veterinary procedure that helps relieve gas in the rumen and prevent further complications.



PRODUCT PARAMETERS

WE ALWAYS ADHERE TO RIGOROUS MANAGEMENT, THE FOUNDATION OF METICULOUS MANUFACTURING, PRODUCE PRODUCTS THAT MEET THEMARKET'S RULES AND CUSTOMER NEEDS

Product name: Veterinary three-purpose trocar

Model: HL-Q8B

Product features: sharp needle tip, easy to operate, strong and dura-

ble, easy to puncture

Product use: used for rumen expansion of ruminants such as cattle

and sheep





Veterinary three-purpose trocar

Needle sharp Easy puncture

The needle tip is sharp, easy to puncture and easy to operate.





Hailian Packaging Equipment Co.,Ltd



0086 13301569240



sales2@dairymachinery.cc



mobilemilkingmachine.com

Nanzhuang Village, Economic Development Zone, Yangshe Twon, Zhangjiagang City, China